FARMER III



Use: Light fitting for the illumination of indoor and outdoor industrial spaces. The light fitting is uncompensated.

Technical description:

The light fitting consists of a ballast box — an AlSi alloy casting and a body made of steel sheet, finished with powder paint. The inorganic glass cover with a seal and protective polycarbonate basket is fixed to the body with four stainless steel caps. The max. cross-section of connecting conductors is 4 mm².

Installation:

On the ceiling, with a suspension eye ø30 mm.

Versions:

Version with a protective steel basket - version "K".

To order:







Protective basket 182.5005 - PMMA 132.2540 - polycarb.



Protective steel basket 1-99.6248



Staninless metal cap 4-99.6180/01

C€		IP54	E27	
Ta -25°C ÷ +55°C (t) -40°C ÷ +40°C (F)			230V 50Hz	
Carton (mm/pcs): 650 x 280 x 290 / 1				

Туре	Recommended light source [W]	Weight[kg]
541 18 01 t	High-pressure mercury discharge lamp HQL 125	7,1
541 18 02 t	High-pressure sodium/halide discharge lamp 70	7,1
541 18 03 F	Halogen lamp HCI-E 150	7,5
541 18 04 F	Halogen lamp HQI-E 100	7,5

^{*}By adding the letter "K" after the type designation, the light fittings will be provided with protective baskets (541 18 01Kt).

JUNIOR





(mm/pcs): 430 x 240 x 240 / 1 K

Use: Light fitting for the illumination of heavy indoor and outdoor industrial spaces with a high level of mechanical stress.

Technical description:

The light fitting body and flange are AlSi alloy castings finished with powder paint. The optical cover is made of tempered glass. There are two cable outlets on the light fitting sides. There is electrical equipment and a reflector built inside the light fitting. The light fitting is designed as a through light fitting, for three-phase connection (five-core cable). When the light fitting is used as a terminal light fitting, the free cable outlet is blinded with a plug. The max. cross-section of the connecting conductors is 4 mm2.

Installation:

With a suspension eye $\varnothing 19$ mm, ceiling holder 4-99.7995, flexible suspension 2-99.5550.

To order:



Shade 254.5021/01



Protective basket 2-99.6195



Flexible suspension



Protective glass



Ceiling holder 4-99.7995

Туре	Recommended light source [W]	Voltage [V/Hz]	Weight [kg]
511 14 07	Halogen bulb Philips EcoClassic 140	230/50	5
	Bulb CLAS 200	230/50	5
	Blended lamp HWL 160	230/50	5
	**High-pressure mercury discharge lamp HQL 180	230/50	5
	***High-pressure mercury discharge lamp HQL 125	230/50	5

^{*}By adding the letter "K" after the type designation, the light fittings will be provided with protective steel baskets (511 14 07K).

^{**}Light fitting provided with a mercury discharge lamp HQL 80W requires a ballast box type BOX 2.

^{***}Light fitting provided with a mercury discharge lamp HQL 125W requires a ballast box type BOX 2.